



Vertical toggle clamp with horizontal base, Type: 2



Order data

| | |
|--------------|---------------|
| Order number | 376508 2 |
| GTIN | 4045197226273 |
| Item class | 32S |

Description

Version:

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Hole spacing e: 12,5 mm

Hole spacing f: 27 mm

Bore \varnothing d: 5.2 mm

Clamping height H: 22.5 mm

Clamping force P1: 1200 N

Clamping force P2: 1500 N

Technical description

| | |
|-------------------|----------|
| Clamping force P1 | 1200 N |
| Contact screw | M6x50 mm |

| | |
|-------------------|------------------------|
| overall height | 140 mm |
| Hole spacing e | 12,5 mm |
| Bore Ø d | 5.2 mm |
| Clamping force P2 | 1500 N |
| Hole spacing f | 27 mm |
| overall length | 74.5 mm |
| Type | 376508 2 |
| Clamping height H | 22.5 mm |
| Type of product | Vertical toggle clamps |