



Push-pull toggle clamp short body, Type: 3



Order data

Order number	376725 3
GTIN	4045197226792
Item class	32S

Description

Version:

Hardened shoulder screws.

- **Ergonomic handle made of oil-resistant plastic.**

Application:

- **Direct fixing to sheet metal fixing points.**
- **Connected to jig body with threaded end of arm.**

Optional extras:

Angled base No. 376735.

Note:

- **Available in stainless steel on request.**

Clamping range: 38 mm

Clamping force P (pressure and traction): 1300 N

Overall height H: 100 mm

Overall length L: 237 mm

Contact screw: M8×50 mm

thread at front of clamp: M20×1.5 mm

Technical description

thread at front of clamp	M20×1.5 mm
Clamping force P (pressure and traction)	1300 N

Clamping range	38 mm
Contact screw	M8x50 mm
Overall height H	100 mm
Overall length L	237 mm
Type	376725 3
Type of product	Push-pull toggle clamp

Accessories

Angled base sturdy Type 2	376735 2
Angled base sturdy Type 3	376735 3