

**Tape measure, Band length: 5m****Order data**

Order number	462010 5
GTIN	4045197207043
Item class	42G

Description**Version:**

Plastic casing with removable belt clip. Automatic tape return and stop, with damping effect. Sliding end hook. Tape measure printed black/red on yellow.

Calibration: G1

Standard: EG II

Tape width: 19 mm

Body length: 74 mm

Body width: 31 mm

Body height: 68 mm

Technical description

Body height	68 mm
Tape width	19 mm
Body length	74 mm
Body width	31 mm
Band length	5 m

Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
DAkkS Calibration locking tape measure 5	026250 5
Calibration Tape measure maximum length 5 m	026240 5