



Universal abrasive cleaner, 80×50×20 mm, Type: M



Order data

| | |
|--------------|---------------|
| Order number | 557660 M |
| GTIN | 4045197241764 |
| Item class | 52E |

Description

Version:

Flexible hand abrasive block with flexibly bonded abrasive grit (long service life, fully usable). Open pore bonding ensures the abrasive body never clogs. Suitable for wet and dry use. Water and oil resistant.

Economy version with corundum (A).

Application:

Multi-purpose for **cleaning, polishing, smoothing, mat finishing** and **abrading all materials**.

Note:

Water, oil, compounds or similar agents **increase the effectiveness**.

Grit designation: medium

Length: 80 mm

Width: 50 mm

Height: 20 mm

Technical description

| | |
|------------------|--------|
| Grit designation | medium |
| Height | 20 mm |
| Width | 50 mm |

| | |
|------------------------|---------------|
| Length | 80 mm |
| Product name attribute | 80×50×20 mm |
| Type of product | Sanding block |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Carbide (HM) | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable only under restricted conditions | | |
| Stone | suitable | | |
| Paint | suitable | | |
| wet maximum | suitable | | |
| dry | suitable | | |