



Universal abrasive cleaner, 80×50×20 mm, Type: F



Order data

Order number	557660 F
GTIN	4045197241771
Item class	52E

Description

Version:

Flexible hand abrasive block with flexibly bonded abrasive grit (long service life, fully usable). Open pore bonding ensures the abrasive body never clogs. Suitable for wet and dry use. Water and oil resistant.

Economy version with corundum (A).

Application:

Multi-purpose for **cleaning, polishing, smoothing, mat finishing** and **abrading all materials**.

Note:

Water, oil, compounds or similar agents **increase the effectiveness**.

Grit designation: fine

Length: 80 mm

Width: 50 mm

Height: 20 mm

Technical description

Grit designation	fine
Width	50 mm
Height	20 mm

Length	80 mm
Product name attribute	80×50×20 mm
Type of product	Sanding block

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
Stone	suitable		
Paint	suitable		
wet maximum	suitable		
dry	suitable		