



## Double open ended spanner, chrome-plated, Jaw widths: 6X7mm



### Order data

Order number	610950 6X7
GTIN	4045197159199
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 122 mm

maximum jaw width b1: 16 mm

maximum jaw width b2: 18 mm

maximum jaw height h: 4 mm

### Technical description

Width across flats 2	7 mm
maximum jaw width b1	16 mm
Width across flats 1	6 mm
maximum jaw height h	4 mm
maximum jaw width b2	18 mm
Width across flats	metric
Spanner length L	122 mm
Standard	DIN 3110
Standard	ISO 3318

Jaw position 1	15 °
Jaw position 2	15 °
Surface	chrome plated
Product name attribute	chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner