

**Double open ended spanner set, chrome-plated, Number of keys: 8****Order data**

Order number	610960 8
GTIN	4045197159403
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22

Technical description

Number of keys	8
Width across flats	metric
Jaw position 1	15°
Jaw position 2	15°
Surface	chrome-plated
Type of product	Spanner

Accessories

Double open ended spanner Jaw widths 14X15 mm	610950 14X15
Double open ended spanner Jaw widths 19X22 mm	610950 19X22
Double open ended spanner Jaw widths 18X21 mm	610950 18X21
Double open ended spanner Jaw widths 10X11 mm	610950 10X11
Double open ended spanner Jaw widths 12X13 mm	610950 12X13
Double open ended spanner Jaw widths 16X17 mm	610950 16X17
Double open ended spanner Jaw widths 8X9 mm	610950 8X9
Plastic clip holder for number of sockets 8	611500 8
Double open ended spanner Jaw widths 6X7 mm	610950 6X7