

Vanadium combination pliers, bright finished, with two-part grips, Overall length: 180 mm



Order data

Order number	702995 180
GTIN	4045197887320
Item class	72B

Description

Version:

Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire.

Jaws bright finished, handles with multi-component covering.

Standard:

DIN ISO 5746

Material:

Chrome vanadium steel, drop forged. Cutting capacity hard wire up to Ø: 2.2 mm

Cutting capacity piano wire up to Ø: 1.8 mm

Technical description

overall length	180 mm
Cutting capacity hard wire up to \varnothing	2.2 mm
Cutting capacity piano wire up to \varnothing	1.8 mm
Standard	DIN ISO 5746
Jaw characteristics	inner face serrated
Handle	With 2K multicomponent cases

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC), pliers body drop forged
Material	Chrome vanadium steel.
Surface	bright finish
non-sparking	no