



Combination spanner, imperial, chrome-plated, Width across flats: 9/16in



Order data

Order number	613970 9/16
GTIN	4045197550088
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 181 mm

maximum jaw height h₁: 6.5 mm

maximum ring height h_{2max}: 12 mm

Technical description

maximum jaw height h ₁	6.5 mm
Spanner length L	181 mm
Width across flats	9/16 in
Width across flats	imperial
maximum ring height h _{2max}	12 mm
Ring setting	15 °
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

