



Combination spanner set, chrome-plated, Number of keys: 19



Order data

Order number	613960 19
GTIN	4045197463807
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

1 each combination spanner No. 613600 / 613500 / 613800 / 613900 / 613950 / 613520 / 613970:
Size 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24

Technical description

Number of keys	19
Width across flats	metric
Ring setting	15°
Material	Chrome vanadium steel
Surface	chrome-plated
Product name attribute	chrome-plated
Type of product	Spanner

Accessories

Combination spanner Width across flats 14 mm	613950 14
Combination spanner Width across flats 18 mm	613950 18
Combination spanner Width across flats 21 mm	613950 21
Combination spanner Width across flats 17 mm	613950 17
Combination spanner Width across flats 13 mm	613950 13
Combination spanner Width across flats 6 mm	613950 6
Combination spanner Width across flats 19 mm	613950 19
Combination spanner Width across flats 15 mm	613950 15
Combination spanner Width across flats 24 mm	613950 24
Combination spanner Width across flats 16 mm	613950 16
Combination spanner Width across flats 9 mm	613950 9
Combination spanner Width across flats 22 mm	613950 22
Combination spanner Width across flats 12 mm	613950 12
Combination spanner Width across flats 20 mm	613950 20
Combination spanner Width across flats 11 mm	613950 11
Combination spanner Width across flats 7 mm	613950 7
Combination spanner Width across flats 10 mm	613950 10
Combination spanner Width across flats 8 mm	613950 8
Combination spanner Width across flats 5,5 mm	613950 5,5