HOLEX

Hand file, Cut 3, Length without tang: 150mm

Order data

Order number	510220 150
GTIN	4045197889133
Item class	52A

Description

Version:

The blanks are forged and ground; manufactured with an exact cut of even density and depth using special machines. These **non-convex files** have tooth profiles appropriate to each grade of file.

Cuts on 3 faces; square end. Application: The quality file for workshop use with long tool life and high removal rate. Standard: DIN 7261 Form A Standard: DIN 7261 Cross section: 16×4 mm

Technical description

Length without tang	150 mm		
Cross section	16×4 mm		
Product name attribute	Cut 3		
Cut	3		
Shape	А		
Shape description	file with plain end		
File surfaces	3		
incl. file handle	no		
Standard	DIN 7261		

Type of product		Engineer's file	
User data			
	Suitability	V,	ISO code

Alu Mg	suitable only under restricted conditions	
Steel < 900 N/mm ²	suitable	
Steel < 1400 N/mm ²	suitable	
Steel < 55 HRC	suitable	
Steel < 60 HRC	suitable only under restricted conditions	
INOX	suitable only under restricted conditions	
GG(G)	suitable	
CuZn	suitable	
Plastic, GRP	suitable	
Wood	suitable	

Accessories

File brush Bristle length L3× width L1 80X20 mm	576000 80X20
Plastic file handle Overall length 90 mm	519510 90
Plastic file handle Overall length 110 mm	519550 110
2-component ergonomic file handle Overall length 110 mm	519600 110
File brush Bristle length L3× width L1 100X25 mm	576000 100X25
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
Hardwood file handle Overall length 120 mm	519400 120
Plastic file handle Overall length 100 mm	519510 100