

Round file, Cut 3, Length without tang: 150 mm

Orc	ler d	data
-----	-------	------

Order number	514220 150	
GTIN 4045197889188		
Item class	52A	

Description

Version:

The blanks are forged and ground; manufactured with an exact cut of even density and depth using special machines. These **non-convex files** have tooth profiles appropriate to each grade of file.

With helical cut; convex end.

Application:

The **quality file** for workshop use with long tool life and high removal rate.

Standard:

DIN 7261 Form F Standard: DIN 7261 Diameter: 5.5 mm

Technical description

Diameter	5.5 mm	
Length without tang	150 mm	
Product name attribute	Cut 3	
Cut 3		
Shape	F	
Shape description	round	
File surfaces	cuts on all faces	
incl. file handle	no	
Standard	DIN 7261	



Type of product Engineer's file

User data

	Suitability	\mathbf{V}_{c}	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		

Accessories

Plastic file handle Overall length 90 mm	519510 90
Hardwood file handle Overall length 100 mm	519400 100
File brush Bristle length L3× width L1 80X20 mm	576000 80X20
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
Plastic file handle Overall length 100 mm	519510 100
Plastic file handle Overall length 110 mm	519550 110
File brush Bristle length L3× width L1 100X25 mm	576000 100X25
2-component ergonomic file handle Overall length 110 mm	519600 110