

**Garant**
**Open ended spanner / ratchet ring spanner, Width across flats: 18mm**

**Order data**

Order number	614800 18
GTIN	4045197160287
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 239 mm

Jaw width b: 38.6 mm

Jaw height  $h_1$ : 8.1 mm

Ring thickness  $h_2$ : 11.2 mm

Ring  $\varnothing$  D: 33.4 mm

Ratchet torque rating: 300 N·m

**Technical description**

Ring thickness $h_2$	11.2 mm
Width across flats	18 mm
Jaw width b	38.6 mm
Spanner length L	239 mm
Jaw height $h_1$	8.1 mm
Ratchet torque rating	300 N·m
Ring $\varnothing$ D	33.4 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner