

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 19mm

Order data

Order number	614800 19
GTIN	4045197160294
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 250 mm

Jaw width b: 40.3 mm

Jaw height h_1 : 8.5 mm

Ring thickness h_2 : 11.5 mm

Ring \varnothing D: 34.5 mm

Ratchet torque rating: 325 N·m

Technical description

Spanner length L	250 mm
Ring thickness h_2	11.5 mm
Ratchet torque rating	325 N·m
Ring \varnothing D	34.5 mm
Jaw height h_1	8.5 mm
Width across flats	19 mm
Jaw width b	40.3 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner

Accessories

Adapter for ratchet ring spanner Type 3	614850 3
---	----------