

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 50mm

Order data

Order number	614800 50
GTIN	4045197511898
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 640 mm

Jaw width b: 96 mm

Jaw height h_1 : 21 mm

Ring thickness h_2 : 26.5 mm

Ring \varnothing D: 88 mm

Ratchet torque rating: 1700 N·m

Technical description

Ring \varnothing D	88 mm
Spanner length L	640 mm
Ratchet torque rating	1700 N·m
Jaw width b	96 mm
Width across flats	50 mm
Jaw height h_1	21 mm
Ring thickness h_2	26.5 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner