

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 14mm

Order data

Order number	614800 14
GTIN	4045197160249
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 193 mm

Jaw width b: 30.9 mm

Jaw height h_1 : 6.6 mm

Ring thickness h_2 : 9.4 mm

Ring \varnothing D: 27.3 mm

Ratchet torque rating: 160 N·m

Technical description

Jaw width b	30.9 mm
Width across flats	14 mm
Ratchet torque rating	160 N·m
Ring \varnothing D	27.3 mm
Jaw height h_1	6.6 mm
Spanner length L	193 mm
Ring thickness h_2	9.4 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner