

**Garant**
**Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 13mm**

**Order data**

Order number	614820 13
GTIN	4045197218780
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 180 mm

Jaw width b: 27.1 mm

Jaw height  $h_1$ : 6 mm

Ring thickness  $h_2$ : 9.3 mm

Ring  $\varnothing$  D: 25.5 mm

Ratchet torque rating: 115 N·m

**Technical description**

Ring $\varnothing$ D	25.5 mm
Ring thickness $h_2$	9.3 mm
Jaw width b	27.1 mm
Width across flats	13 mm
Jaw height $h_1$	6 mm
Ratchet torque rating	115 N·m
Spanner length L	180 mm
Width across flats	metric

Ring setting	15 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner

---

## Accessories

Adapter for ratchet ring spanner Type 2	614850 2
---	----------