

Garant
Open ended spanner / ratchet ring spanner set, imperial, Width across flats: 1/4in

Order data

Order number	614825 1/4
GTIN	4045197331205
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 136 mm

Jaw width b: 17.1 mm

Jaw height h_1 : 4.3 mm

Ring thickness h_2 : 7 mm

Ring \varnothing D: 17.3 mm

Ratchet torque rating: 20 N·m

Technical description

Jaw height h_1	4.3 mm
Spanner length L	136 mm
Ratchet torque rating	20 N·m
Ring thickness h_2	7 mm
Jaw width b	17.1 mm
Ring \varnothing D	17.3 mm
Width across flats	1/4 in
Width across flats	imperial

Ring setting	0 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner