

**Garant**
**Open ended spanner / ratchet ring spanner set, imperial, Width across flats: 3/8in**

**Order data**

Order number	614825 3/8
GTIN	4045197331229
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 160 mm

Jaw width b: 22 mm

Jaw height  $h_1$ : 5.2 mm

Ring thickness  $h_2$ : 7.7 mm

Ring  $\varnothing$  D: 20.8 mm

Ratchet torque rating: 70 N·m

**Technical description**

Spanner length L	160 mm
Ring $\varnothing$ D	20.8 mm
Ratchet torque rating	70 N·m
Width across flats	3/8 in
Ring thickness $h_2$	7.7 mm
Jaw height $h_1$	5.2 mm
Jaw width b	22 mm
Width across flats	imperial

Ring setting	0 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner