

Garant
Open ended spanner / ratchet ring spanner set, imperial, Width across flats: 7/16in

Order data

Order number	614825 7/16
GTIN	4045197331236
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 168 mm

Jaw width b: 24 mm

Jaw height h_1 : 5.3 mm

Ring thickness h_2 : 8.3 mm

Ring \varnothing D: 22.5 mm

Ratchet torque rating: 80 N·m

Technical description

Ratchet torque rating	80 N·m
Spanner length L	168 mm
Jaw height h_1	5.3 mm
Jaw width b	24 mm
Ring \varnothing D	22.5 mm
Ring thickness h_2	8.3 mm
Width across flats	7/16 in
Width across flats	imperial

Ring setting	0 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner