

**Garant**

**Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 9mm**


**Order data**

Order number	614820 9
GTIN	4045197218742
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 143 mm

Jaw width b: 19.3 mm

Jaw height  $h_1$ : 5 mm

Ring thickness  $h_2$ : 7.6 mm

Ring  $\varnothing$  D: 19 mm

Ratchet torque rating: 40 N·m

**Technical description**

Ring thickness $h_2$	7.6 mm
Ring $\varnothing$ D	19 mm
Jaw width b	19.3 mm
Width across flats	9 mm
Ratchet torque rating	40 N·m
Jaw height $h_1$	5 mm
Spanner length L	143 mm
Width across flats	metric

Ring setting	15 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner