

**Garant****Circular saw blade, wood, alternating teeth medium, Blade Ø D: 400mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 584035 400    |
| GTIN         | 4045197220806 |
| Item class   | 51S           |

**Description****Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

**Application:**

For circular, cross-cut, compound, and mitre saws.

Type UW for **board materials, veneered or plastic coated on one side**, veneer packs longitudinally, hard paper and hard fabric.

**Note:**

**Further circular saw blades can be found in Group 17.**

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm

Number of teeth: 60

Width of cut B: 3.5 mm

**Technical description**

|           |        |
|-----------|--------|
| Blade Ø D | 400 mm |
| Bore Ø    | 30 mm  |

|                                   |                                  |
|-----------------------------------|----------------------------------|
| Number of teeth                   | 60                               |
| Width of cut B                    | 3.5 mm                           |
| Drive holes number/Ø/pitch circle | 2/7/42 and 2/9/46 and 2/10/60 mm |
| Type of product                   | Circular saw blade               |