

## Garant

### Screwdriver for slot-head, with 2-component Haptoprene handle, Blade width b: 3,5 mm



#### Order data

Order number	660030 3,5
GTIN	4045197923080
Item class	61F

#### Description

##### Version:

Versatile, robust screwdriver with taper blade.

The special surface structure allows transmission of high torques, even with wet or oily hands.

**Blade** of chrome vanadium special alloy combining maximum hardness and exceptional toughness.

Surface nickel-plated and chrome-plated, with black plane parallel stepped tip.

**Power grip** with non-allergenic, easy-grip **Haptoprene** surface and a core of particularly tough and impact-resistant polypropylene. **From size 8 with hexagon flats for wrench assistance.**

- **Stepped plane parallel tips match screw head slot sizes exactly.**
- **Smooth, burr-free rounding of the end of the handle prevents friction in the palm of the hand.**
- **Rounded ergonomic shape with comfortable easy-grip surface ensures non-fatiguing working and high torque transmission.**
- **Non-roll flats.**
- **Marked with drive symbol and size.**

##### Advantage:

- **Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission.**
- **No cam-out effect.**
- **Tips perfectly fit standard and non-standard screw slot sizes.**
- **Smooth, burr-free rounding of the end of the handle prevents friction in the palm of the hand.**
- **Rounded ergonomic shape with comfortable easy-grip surface ensures non-fatiguing working and high torque transmission.**
- **Non-roll flats.**
- **Marked with drive symbol and size.**

##### Application:

For repair and assembly work, for loosening tight screws etc.

Blade designation: 1

Tip thickness a: 0.5 mm

Blade length: 90 mm

overall length: 180 mm

---

## Technical description

Blade length	90 mm
Blade width b	3.5 mm
Blade designation	1
Tip thickness a	0.5 mm
overall length	180 mm
Drive profile	Slot-head screwdriver
Type of product	Screwdrivers