

Garant

Diagonal side cutter chrome-plated, with grips, overall length: 160 mm


Order data

Order number	724840 160
GTIN	4045197417022
Item class	71B

Description
Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Jaws chrome-plated, handles with ergonomically optimised multi-component covering, with non-slip **Haptoprene®** surface.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Cutting capacity soft wire up to \varnothing : 2.8 mm

Cutting capacity hard wire up to \varnothing : 2 mm

Technical description

overall length	160 mm
Cutting capacity soft wire up to \varnothing	2.8 mm
Cutting capacity hard wire up to \varnothing	2 mm
Standard	DIN ISO 5749
Handle	Multi-component covering with non-slip Haptoprene surface
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel

Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers