

**Diagonal side cutter, bright finish, overall length: 160 mm****Order data**

Order number	725250 160
GTIN	4045197166326
Item class	72B

**Description****Version:**

Slim shape with induction hardened cutting edges (approx. 62 HRC).  
Jaws bright finished, plastic coated handles.

**Standard:**

**DIN ISO 5749**

**Material:**

Chrome vanadium steel, drop-forged and oil-hardened.  
Cutting capacity soft wire up to  $\varnothing$ : 2.8 mm  
Cutting capacity hard wire up to  $\varnothing$ : 2 mm

**Technical description**

Cutting capacity soft wire up to $\varnothing$	2.8 mm
Cutting capacity hard wire up to $\varnothing$	2 mm
overall length	160 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	bright finish

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers