



Vanadium combination pliers, bright finished, overall length: 180mm



Order data

Order number	703000 180
GTIN	4045197166005
Item class	72B

Description

Version:

Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire.

Jaws bright finished, plastic coated handles.

Standard:

DIN ISO 5746

Material:

Chrome vanadium steel, drop forged.

Cutting capacity hard wire up to \varnothing : 2.2 mm

Cutting capacity piano wire up to \varnothing : 1.8 mm

Technical description

Cutting capacity piano wire up to \varnothing	1.8 mm
Cutting capacity hard wire up to \varnothing	2.2 mm
overall length	180 mm
Standard	DIN ISO 5746
Jaw characteristics	inner face serrated
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC), pliers body drop forged

Material	Chrome vanadium steel
Surface	bright finish
non-sparking	no
Type of product	Multi-function pliers