

**Garant**
**Bits set 61 pieces**

**Order data**

Order number	676040
GTIN	4045197613349
Item class	61F

**Description**
**Version:**

System box of virtually indestructible ABS plastic with integral hinges and snap fastener. The bits are widely spaced so that when the box is open they can be easily accessed and taken out.

**Content:**

Bits C 6.3 (1/4 inch) set; 1 coupling shank.

**Content:**

Bits, length 25 mm, C 6.3, for Phillips: No. 675105 3 pcs. size 1/25; 6 pcs. size 2/25; 2 pcs. size 3/25  
 Bits, length 25 mm, C 6.3, for Pozidriv: No. 675115 3 pcs. size 1/25; 6 pcs. size 2/25; 2 pcs. size 3/25  
 Bits, length 25 mm, C 6.3, for slot-head: 1 pc. each size 0.5×4; 0.6×4.5; 1.0×5.5; 1.2×6.5  
 Bits, length 25 mm, C 6.3, for internal Torx®: No. 675155 1 pc. size TX5; TX6; TX7; TX8; TX9; TX10; TX15; TX20; TX25; TX27; TX30; TX40  
 Bits, length 25 mm, C 6.3, for internal Torx® with pin: 1 each size TX10; TX15; TX20; TX25; TX27; TX30; TX40  
 Bits, length 25 mm, C 6.3, for hex socket: No. 675125 1 pc. size 2; 2.5; 3; 4; 5; 6  
 Bits, length 25 mm, C 6.3, for hex socket, with ball point: 1 pc. each size 2.5; 3; 4; 5; 6  
 Bits, length 25 mm, C 6.3, for TRI-WING®: 1 pc. each size 2; 3; 4; 5  
 Quick-release adaptor: 1 pc. No. 675050 size 6.3

**Technical description**

Bit hexagon shank	C 6,3
Height	47 mm
Width	85 mm
Length	127 mm
Drive profile	Screwdriver for Phillips
Drive profile	Hexagon screwdriver
Drive profile	TriWing screwdriver
Drive profile	Pozidriv screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Screwdriver for TORX® screws with hole
Packaging	ABS plastic box
Number of pieces	61
Type of product	Bit tool

## Accessories

Modular box Type 21-1	630320 21-1
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX15	675155 TX15
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX10	675155 TX10
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 3 mm	675125 3
Bit for Pozidriv, 1/4 inch, with torsion zone Cross-head size / overall length 1/25 mm	675115 1/25
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX7	675155 TX7
Bit for Pozidriv, 1/4 inch, with torsion zone Cross-head size / overall length 2/25 mm	675115 2/25
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX8	675155 TX8
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 4 mm	675125 4
	675050 6,3

Shank with magnet / quick-change coupling Hexagon shank 6,3

Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX40	675155 TX40
Bit for slot-head, 1/4 inch, with torsion zone Cross-head size / overall length 3/25 mm	675105 3/25
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX6	675155 TX6
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX9	675155 TX9
Bit for Pozidriv, 1/4 inch, with torsion zone Cross-head size / overall length 3/25 mm	675115 3/25
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX20	675155 TX20
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 6 mm	675125 6
Bit for slot-head, 1/4 inch, with torsion zone Cross-head size / overall length 2/25 mm	675105 2/25
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 2 mm	675125 2
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 5 mm	675125 5
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX27	675155 TX27
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX25	675155 TX25
Bit for slot-head, 1/4 inch, with torsion zone Cross-head size / overall length 1/25 mm	675105 1/25
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX30	675155 TX30
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 2,5 mm	675125 2,5
Bit for Torx®, 1/4 inch, with torsion zone Torx® profile TX5	675155 TX5