

# Snipe nose pliers, straight, chrome-plated, with grips, overall length: 160 mm



## **Order data**

Order number	713040 160
GTIN	4045197373540
Item class	71B

# **Description**

## **Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

#### **Standard:**

### **DIN ISO 5745**

#### **Material:**

Chrome vanadium steel, drop-forged and oil-hardened.

Jaw length: 50 mm

# **Technical description**

overall length	160 mm
Jaw length	50 mm
Handle	Multi-component covering with non-slip Haptoprene surface
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened



Material	Chrome vanadium steel, drop- forged and oil-hardened
Surface	chrome-plated
Type of product	Multi-function pliers