



Snipe nose pliers, angled, bright finished, overall length: 200 mm



Order data

Order number	713600 200
GTIN	4045197166098
Item class	72B

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws bright finished, plastic coated handles.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Jaw length: 73 mm

Technical description

overall length	200 mm
Jaw length	73 mm
Jaw design	snipe-nosed, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Handle	plastic coated
Material	Chrome vanadium steel, drop-forged and oil-hardened

Surface	bright finish
Type of product	Multi-function pliers