

**Garant****Precision circlip pliers, Type: A21****Order data**

Order number	719870 A21
GTIN	4045197504166
Item class	71B

**Description****Version:**

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles. Joint with **integral opening spring**. **Form B –90° angled jaws**.

**Advantage:**

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

**Application:**

For fitting and removing circlips.

**Standard:**

**DIN 5254 A und B** – für Außensicherungsringe.

Use of circlip pliers: Outer ring, angled

overall length: 165 mm

for external circlips Ø: 19 - 60 mm

Tip Ø: 1.8 mm

**Technical description**

Shape	B
for external circlips Ø	19 - 60 mm
overall length	165 mm

Tip Ø	1.8 mm
Standard	DIN 5254 B
Use of circlip pliers	Outer ring, angled
Jaw shape	90° angled
Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	black
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers