

Garant**Tape measure, Length: 3m****Order data**

Order number	461900 3
GTIN	4045197949264
Item class	41H

Description**Version:**

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return.

For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**.

Plain bearings with Teflon ensure smooth action and exceptionally easy running.

Innovative dampers of special rubber absorb the reaction energy and protect the wrist.

Aluminium profile inserted on the underside for precise standing.

A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

mm graduation

Calibration: G1

Standard: EG II

Tape width: 13 mm

Body length: 62 mm

Body width: 26 mm

Body height: 59 mm

Technical description

Tape width	13 mm
Band length	3 m
Body width	26 mm
Body height	59 mm
Body length	62 mm
Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
DAkkS Calibration locking tape measure 5	026250 5
Calibration Tape measure maximum length 5 m	026240 5