

Garant
Horizontal toggle clamp, variable, Type: 70

Order data

Order number	376400 70
GTIN	4045197953322
Item class	31M

Description
Version:

With horizontal base. Completely black nickel-plated, with solid rivets. Ergonomic 2-component handle. Captive contact screw. Complete with black nickel-plated contact screw.

Advantage:

Stepless adjustment function for variations in workpiece heights. Consistently high clamping forces.

Clamping force: 3000 N

automatic height adjustment S: 35 mm

maximum clamping height: 60 mm

Contact screw: M8×66 mm

Technical description

Clamping force	3000 N
maximum clamping height	60 mm
Contact screw	M8×66 mm
automatic height adjustment S	35 mm
Type of product	Horizontal toggle clamp

