

Garant**Horizontal toggle clamp, variable, Type: 20****Order data**

Order number	376400 20
GTIN	4045197953308
Item class	31M

Description**Version:**

With horizontal base. Completely black nickel-plated, with solid rivets. Ergonomic 2-component handle. Captive contact screw. Complete with black nickel-plated contact screw.

Advantage:

Stepless adjustment function for variations in workpiece heights. Consistently high clamping forces.

Clamping force: 2000 N

automatic height adjustment S: 20 mm

maximum clamping height: 35 mm

Contact screw: M6×49 mm

Technical description

Contact screw	M6×49 mm
maximum clamping height	35 mm
Clamping force	2000 N
automatic height adjustment S	20 mm
Type of product	Horizontal toggle clamp

