

**Garant**
**Push-pull toggle clamp, variable, Type: 25**

**Order data**

Order number	376410 25
GTIN	4045197953346
Item class	31M

**Description**
**Version:**

With horizontal base. Completely black nickel-plated, with solid rivets. Ergonomic 2-component handle. Captive contact screw. Complete with black nickel-plated contact screw.

**Advantage:**

Stepless adjustment function for variations in workpiece heights. Consistently high clamping forces.

Clamping force: 3000 N

automatic height adjustment S: 13 mm

maximum clamping height: 35 mm

Contact screw: M8×50 mm

**Technical description**

maximum clamping height	35 mm
Clamping force	3000 N
Contact screw	M8×50 mm
automatic height adjustment S	13 mm
Type of product	Push-pull toggle clamp

