

**Garant****Push-pull toggle clamp, variable, Type: 15****Order data**

Order number	376410 15
GTIN	4045197953339
Item class	31M

**Description****Version:**

With horizontal base. Completely black nickel-plated, with solid rivets. Ergonomic 2-component handle. Captive contact screw. Complete with black nickel-plated contact screw.

**Advantage:**

Stepless adjustment function for variations in workpiece heights. Consistently high clamping forces.

Clamping force: 2000 N

automatic height adjustment S: 8 mm

maximum clamping height: 25 mm

Contact screw: M6×37 mm

**Technical description**

maximum clamping height	25 mm
Contact screw	M6×37 mm
Clamping force	2000 N
automatic height adjustment S	8 mm
Type of product	Push-pull toggle clamp

