

**Lightweight malleable cast iron screw clamp, Jaw capacity: 150mm****Order data**

Order number	860200 150
GTIN	4008158004105
Item class	82C

Description**Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. With plastic protective cover on the clamping jaw.

Standard:**DIN 5117**

Cross section of the slide rail: 15×5 mm

Throat: 50 mm

Technical description

Jaw capacity	150 mm
Cross section of the slide rail	15×5 mm
Throat	50 mm
Type of product	Clamp