

**Lightweight malleable cast iron screw clamp, Jaw capacity: 400mm****Order data**

Order number	860200 400
GTIN	4008158014555
Item class	82C

Description**Version:**

High quality malleable cast iron clamping arms; strong prismatic steel slide beam, knurled, electro-galvanised. Smooth running steel spindle, burnished with trapezoidal thread and movable jaw. Instant (high speed) adjustment, reliable clamping. With plastic protective cover on the clamping jaw.

Standard:**DIN 5117**

Cross section of the slide rail: 29×9 mm

Throat: 120 mm

Technical description

Cross section of the slide rail	29×9 mm
Jaw capacity	400 mm
Throat	120 mm
Type of product	Clamp