# HOLEX

All-steel lever clamp, Jaw capacity: 120mm



## Order data

Order number	860650 120
GTIN	4045197494405
Item class	82C

### Description

#### Version:

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Clamping lever with self-locking ratchet clamping mechanism. Opens by releasing the ratchet. Movable pressure pad, clamping lever powder coated.

#### **Application:**

For fast and easy clamping with high clamping pressure.

Cross section of the slide rail: 13.5×6.5 mm Throat: 60 mm Weight: 0.5 kg

# **Technical description**

Cross section of the slide rail	13.5×6.5 mm
Jaw capacity	120 mm
Weight	0.5 kg
Throat	60 mm

Type of product

Clamp