

**All-steel clamp, Jaw capacity: 300mm****Order data**

Order number	860550 300
GTIN	4045197335401
Item class	82C

Description**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread and moving jaw anvil. Spindle burnished. With plastic protective cap.
Cross section of the slide rail: 25.5×12 mm
Throat: 120 mm

Technical description

Throat	120 mm
Jaw capacity	300 mm
Cross section of the slide rail	25.5×12 mm
Type of product	Clamp

