



Universal clamp (clamping hand), Type: 25



Order data

Order number	861900 25
GTIN	4045197167514
Item class	82C

Description

Version:

With trapezoidal thread spindle and 2 swing clamping jaws. Each clamping jaw has 3 smooth faces and a cross-Vee face; can be used for **clamping the most diverse components.**

Application:

For **internal** and **external clamping** of the most diverse workpiece shapes.

Material:

Spindle and clamping block of burnished steel.

Capacity in compression a: 0 - 25 mm

Capacity in tension b: 20 - 48 mm

Clamping depth c: 15 mm

maximum clamping force: 1000 N

Technical description

maximum clamping force	1000 N
Capacity in tension b	20 - 48 mm
Clamping depth c	15 mm
Capacity in compression a	0 - 25 mm
Type of product	Clamp

