

**HOLEX****All-steel high-performance clamp with special jaw anvil, Jaw capacity: 800mm****Order data**

Order number	861120 800
GTIN	4045197657411
Item class	82C

**Description****Version:**

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanized. Slide jaw made of steel, drop-forged, tempered, and electro-galvanized. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay, can tilt through 35°. Spindle tempered and burnished with adjustable clamp handle.

**Application:**

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces up to 35°. **Maximum clamping pressure up to approx. 12000 N.**

Cross section of the slide rail: 30×15 mm

Throat: 140 mm

Weight: 4.6 kg

**Technical description**

Weight	4.6 kg
Throat	140 mm

Jaw capacity	800 mm
Cross section of the slide rail	30×15 mm
Type of product	Clamp

---

## Accessories

Pressure plate Type GSV	861121 GSV
Pressure plate Type GSP	861121 GSP