

Garant
Four-way ratchet ring spanner "4 in 1", Type: 8-13

Order data

Order number	614847 8-13
GTIN	4045197967787
Item class	61B

Description
Version:

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Width across flats 1: 8 mm

Width across flats 2: 10 mm

Width across flats 3: 12 mm

Width across flats 4: 13 mm

overall length L: 150 mm

maximum ring \varnothing D1: 20.2 mm

Technical description

maximum ring \varnothing D1	20.2 mm
Width across flats	metric
Width across flats 2	10 mm
maximum ring height h_2	16.8 mm
maximum ring \varnothing D2	24.8 mm
overall length L	150 mm
Width across flats 4	13 mm
Width across flats 3	12 mm

maximum ring height h_1	13.8 mm
Width across flats 1	8 mm
No. of teeth	72
Working arc	5 °
Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner