

Garant
Soft-faced hammer with rubber inserts, black, Housing Ø / material: 60Gmm

Order data

Order number	752500 60G
GTIN	4045197977410
Item class	71D

Description
Version:

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Head length with inserts: 149 mm

Striking face Ø of the inserts: 60 mm

Handle length: 335 mm

Overall length: 410 mm

Weight without inserts: 940 g

Technical description

Overall length	410 mm
Handle length	335 mm
Weight without inserts	940 g
Head length with inserts	149 mm
Striking face Ø of the inserts	60 mm

Colour	black
dead-blow	yes
Inserts can be combined	yes
Type of product	Hammer

Accessories

Plastic insert, medium hard for soft-faced hammer 60	752550 60
Nylon insert, hard for soft-faced hammer 60	752560 60
Rubber insert, soft for soft-faced hammer 60	752540 60
Hickory hammer handle for body Ø 60 mm	752530 60