

Garant**Soft-faced hammer with rubber inserts, black, Housing Ø / material: 40Gmm****Order data**

Order number	752500 40G
GTIN	4045197976598
Item class	71D

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Head length with inserts: 116 mm

Striking face Ø of the inserts: 40 mm

Handle length: 275 mm

Overall length: 330 mm

Weight without inserts: 418 g

Technical description

Overall length	330 mm
Striking face Ø of the inserts	40 mm
Weight without inserts	418 g
Head length with inserts	116 mm
Handle length	275 mm

Colour	black
dead-blow	yes
Inserts can be combined	yes
Type of product	Hammer

Accessories

Nylon insert, hard for soft-faced hammer 40	752560 40
Plastic insert, medium hard for soft-faced hammer 40	752550 40
Rubber insert, soft for soft-faced hammer 40	752540 40
Hickory hammer handle for body Ø 40 mm	752530 40