

Garant**Soft-faced hammer with plastic inserts, red, Housing Ø / material: 40Gmm****Order data**

| | |
|--------------|---------------|
| Order number | 752510 40G |
| GTIN | 4045197977007 |
| Item class | 71D |

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Head length with inserts: 116 mm

Striking face Ø of the inserts: 40 mm

Handle length: 275 mm

Overall length: 330 mm

Weight without inserts: 418 g

Technical description

| | |
|--------------------------------|--------|
| Striking face Ø of the inserts | 40 mm |
| Head length with inserts | 116 mm |
| Weight without inserts | 418 g |
| Handle length | 275 mm |
| Overall length | 330 mm |

| | |
|-------------------------|--------|
| Colour | red |
| dead-blow | yes |
| Inserts can be combined | yes |
| Type of product | Hammer |

Accessories

| | |
|--|-----------|
| Plastic insert, medium hard for soft-faced hammer 40 | 752550 40 |
| Hickory hammer handle for body Ø 40 mm | 752530 40 |
| Nylon insert, hard for soft-faced hammer 40 | 752560 40 |
| Rubber insert, soft for soft-faced hammer 40 | 752540 40 |