

Garant
Soft-faced hammer with plastic inserts, red, Housing Ø / material: 50Gmm

Order data

Order number	752510 50G
GTIN	4045197977014
Item class	71D

Description
Version:

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Head length with inserts: 138 mm

Striking face Ø of the inserts: 50 mm

Handle length: 310 mm

Overall length: 380 mm

Weight without inserts: 785 g

Technical description

Handle length	310 mm
Overall length	380 mm
Head length with inserts	138 mm
Weight without inserts	785 g
Striking face Ø of the inserts	50 mm

Colour	red
dead-blow	yes
Inserts can be combined	yes
Type of product	Hammer

Accessories

Hickory hammer handle for body Ø 50 mm	752530 50
Nylon insert, hard for soft-faced hammer 50	752560 50
Rubber insert, soft for soft-faced hammer 50	752540 50
Plastic insert, medium hard for soft-faced hammer 50	752550 50