

Garant
Soft-faced hammer with rubber inserts, black, Housing Ø / material: 80Gmm

Order data

Order number	752500 80G
GTIN	4045197992291
Item class	71D

Description
Version:

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Head length with inserts: 175 mm

Striking face Ø of the inserts: 80 mm

Handle length: 400 mm

Overall length: 500 mm

Weight without inserts: 1895 g

Technical description

Head length with inserts	175 mm
Overall length	500 mm
Handle length	400 mm
Striking face Ø of the inserts	80 mm
Weight without inserts	1895 g

Colour	black
dead-blow	yes
Inserts can be combined	yes
Type of product	Hammer

Accessories

Hickory hammer handle for body Ø 80 mm	752530 80
Nylon insert, hard for soft-faced hammer 80	752560 80
Rubber insert, soft for soft-faced hammer 80	752540 80