



## LED pen torch with batteries, Type: CRI-PEN



### Order data

Order number	081461 CRI-PEN
GTIN	4062406056896
Item class	02A

### Description

**Version:**

LED pen torch with focussable lamp head, pocket clip and push-button. True colour LED with **high CRI value** (> 95) for recognition of colour matching.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Supplied with 2 × AAA batteries.

IP Index of Protection: IP 54

Torch function: Focus

ATEX zone: no

Illumination: 100 lm

Working life: 2 h

CRI value: 95

Number of batteries contained: 2

Battery type: Micro, AAA

### Technical description

IP Index of Protection	IP 54
Bulb	LED module
ATEX zone	no
Working life	2 h
Number of batteries contained	2
Battery type	Micro, AAA
Illumination	100 lm
Weight	60 g
Torch function	Focus
CRI value	95
Overall length	135 mm
Overall width	17 mm
Power supply	Battery-powered
Type of product	Flashlight

## Accessories

Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline manganese battery set International size LR3	081557 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline manganese battery set International size LR3	081558 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081553 LR3