



Adjustable spanner with coated handle, overall length: 150 mm



Order data

Order number	813961 150
GTIN	4062406069681
Item class	82A

Description

Version:

Slim design with double-T-profile shank (chromium plated). Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

With non-slip grip.

Adjustable spanner, chrome-plated.

maximum width across flats: 19 mm

overall length: 6 in

Technical description

overall length	150 mm
maximum width across flats	19 mm
overall length	6 in
Jaw position	22 °
non-sparking	no
Scaling	yes
Grips	yes
Type of product	Adjustable spanners

