



Adjustable spanner, overall length: 100mm



Order data

Order number	814001 100
GTIN	4062406072049
Item class	82A

Description

Version:

Slim design with double-T-profile shank (chromium plated). Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

Adjustable spanner, chrome-plated.
 maximum width across flats: 13 mm
 overall length: 4 in

Technical description

overall length	4 in
maximum width across flats	13 mm
overall length	100 mm
Jaw position	22°
Manufacturing process	drop-forged and hardened
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

